

FASTMOVER CHANNELS

FastMover Channels are vertical storage channels, ideal for organised storage and automatic dispensing of your fast moving products.

FastMover Channels are independent operating units.



A Fastmover Channel consists of a vertical channel with an automatic dispensing unit. The standard channel lengths are 1200, 1600, 1800, 2000 or 2200mm. Other lengths are available. The width can be chosen and adjusted to the selected package width. The FastMover channels can be controlled by an existing robot or by independent operating software.

How it works

In the software products can be allocated to channels by selecting a channel and scanning a product. After that the channel can be filled with packs. The filling is fast and efficient by filling stacks. The FastMover channels can dispense automatically on a conveyor.

Benefits

- **Big storage capacity for fast movers.** A FastMover channel contains approx. 5 to 10 times more packs than a horizontal channel.
- **Automatic and fast dispensing on a conveyor.**
- **Less different channels necessary for the same storage capacity.**
- **Compact: Efficient use of space in your robot or as a standalone module.**
- **Fast filling by filling stacks.**

Application

FastMover channels can be used standalone or in combination with a horizontal channel robot, which can be equipped with slow mover doors.


FastMover channels can be used in one small group of just a few pieces or alternatively in large groups of several hundred FastMover channels.

Application in community pharmacies, hospital pharmacies, central filling pharmacies, pharmaceutical wholesalers etc.




Configurations

- **1 line parallel to a wall**




- **A-form:** 2 lines parallel to each other with dispensing sides facing each other.







- **M-form:** Multiple A- form groups placed parallel to each other.




- **1 line parallel in a RP20 robot**




- **1 line to the head side of a RP20 robot**



- 1 line parallel in a RP30 or RP50 robot



- 1 line to the head side of a RP30 or RP50 robot



More information?

Interested to know how FastMover channels can help to optimise your business?

Contact RoboPharma at tel: +31 (0)416 34 71 72 or sales@robopharma.com



RoboPharma B.V.

P.O. Box 653, 5140 AR Waalwijk
 Havenweg 14, 5145 NJ Waalwijk
 The Netherlands
 Tel: +31 (0)416 34 71 72
 Fax: +31 (0)416 65 18 85

www.robopharma.com
info@robopharma.com

Pharmasee 3000

Daresbury Science & Innovation Centre
 Sci-Tech Daresbury
 Keckwick Lane, Warrington
 Cheshire WA4 4FS
 Tel: +44 (0)1925 607 217

www.pharmasee3000.co.uk
info@pharmasee3000.co.uk

PHARMACY AUTOMATION

